

Garant GRIDLINE

Casing 24G with door hinged on the right, for individual configuration with drawers, 20×20G, Height / door height: 900/625mm**Order data**

Order number	927725 900/625
GTIN	4062406111755
Item class	9GG

Description**Version:**

24G casing with cupboard, for individual configuration with drawers in sturdy steel construction. Can be locked centrally with cylinder lock. Door hinged on the right.

Fitted with:

Number of height-adjustable storage shelves: 1

Colour:

Body RAL 7035 light grey, door RAL 7016 anthracite **powder-coated**.

Note:

When equipping the cabinet with drawers, check that the sum of the individual drawer front heights adds up to the usable cabinet height.

Sizes 600/425 and 700/525 suitable only for Ready-to-go workbenches.

Technical description

Depth	650 mm
Usable width	550 mm

Door usable height	625 mm
Width	600 mm
Door stop	right-hand
Weight	36 kg
Height	900 mm
Usable height for drawers	150 mm
Number of height-adjustable shelves	1
Version	for individual configuration
Material thickness	1 mm
Door opening angle	180 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20×20G
Type of product	Workbench casing

Accessories

Drawer Drawer front height 75 mm	927800 75
Shelf carriers for shelves of workbenches Type 12	927094 12
Drawer Drawer front height 50 mm	927800 50
Slide handle for GridLine Type KO12	914226 KO12
Fixed shelf, galvanized Type 1	927815 1
Pull-out shelf Type 1	927810 1
One-hand individual drawer release system Drawer usable width in G 20	951020 20
Drawer Drawer front height 100 mm	927800 100