

Garant GRIDLINE

**Sliding doors set, Drawer width 2×36G, Height including frame: 1000mm****Order data**

Order number	935635 1000
GTIN	4062406111588
Item class	9GK

**Description****Version:**

The doors are reinforced on the inside and run on ball bearing guides in rails. Lockable by slide handle with a **cylinder lock**. The front fittings kit consists of 2 side stops, 2 guide rails, and 2 door leaves. The shelf bays behind the sliding doors can be fitted with storage shelves, drawers, and pull-out shelves (exception: behind sliding doors No. 935640 only storage shelves can be fitted, no drawers or pull-out shelves).

**Colour:**

Frame RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

**Technical description**

Frame depth	80 mm
Usable height	900 mm
Height including frame	1000 mm
Application range	Drawer/shelf combination unit
Material thickness	1.2 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Drawer width 2×36G
Type of product	Sliding door