

Garant GRIDLINE

Sliding doors set, Drawer width 2×36G, Height including frame: 1500mm



Order data

Order number	935635 1500
GTIN	4062406111601
Item class	9GK

Description

Version:

The doors are reinforced on the inside and run on ball bearing guides in rails. Lockable by slide handle with a **cylinder lock**. The front fittings kit consists of 2 side stops, 2 guide rails, and 2 door leaves. The shelf bays behind the sliding doors can be fitted with storage shelves, drawers, and pull-out shelves (exception: behind sliding doors No. 935640 only storage shelves can be fitted, no drawers or pull-out shelves).

Colour:

Frame RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Technical description

Height including frame	1500 mm
Usable height	1400 mm
Frame depth	80 mm
Application range	Drawer/shelf combination unit
Material thickness	1.2 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Product name attribute	Drawer width 2×36G
Type of product	Sliding door