

Garant GRIDLINE

## Sliding doors set, Drawer width 56G, Height including frame: 1000mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 935640 1000   |
| GTIN         | 4062406111618 |
| Item class   | 9GK           |

### Description

#### Version:

The doors are reinforced on the inside and run on ball bearing guides in rails. Lockable by slide handle with a **cylinder lock**. The front fittings kit consists of 2 side stops, 2 guide rails, and 2 door leaves. The shelf bays behind the sliding doors can be fitted with storage shelves, drawers, and pull-out shelves (exception: behind sliding doors No. 935640 only storage shelves can be fitted, no drawers or pull-out shelves).

#### Colour:

Frame RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

### Technical description

|                        |  |
|------------------------|--|
| Frame depth            | 80 mm  |
| Height including frame | 1000 mm  |
| Usable height          | 900 mm   |
| Application range      | Drawer/shelf combination unit                                  |
| Material thickness     | 1.2 mm   |
| Cylinder lock          | modular barrel   |
| Colour selection       | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |

|                        |                  |
|------------------------|------------------|
| Product name attribute | Drawer width 56G |
| Type of product        | Sliding door     |