

Garant GRIDLINE

Drawer, 20×20G, Drawer front height: 150mm**Order data**

Order number	927800 150
GTIN	4062406111830
Item class	9GG

Description**Version:**

100% full extension drawers in sturdy steel construction, with differential runners and 75 kg load capacity. Aluminium handles with labelling strips that can be exchanged and rewritten. New type of drawer concept for optimum equipment with dividing material.

Suitable for:

All 24G casings.

Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Front height	150 mm
Weight	10 kg
Drawer usable area in G	20×20
Drawer/pull-out shelf load capacity	75 kg
Usable height	125 mm
Usable depth in G	20
Usable width in G	20
Application range	Workbench casing
Usable width	500 mm

Usable depth	500 mm
with individual drawer release system	no
Material thickness	1 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7016, 5012, 5005
Drawer usable width × usable depth in G	20×20G
Type of product	Drawer