

Garant GRIDLINE

**24G casing, mobile, for individual configuration with drawers, 20×20G,  
Height of the housing: 700mm****Order data**

Order number	927730 700
GTIN	4062406111786
Item class	9GG

**Description****Version:**

24G casing, mobile, for individual configuration with drawers in sturdy steel construction. Covering with a ribbed rubber mat, raised edge and 2-component Haptoprene® push handles. With 2 each ball-bearing fixed wheels and castors, (castors with brakes for the wheels and the castor heads) Ø 125 mm, with treadless polyurethane tyres, minimum rolling resistance, low noise and fibre shields.

Can be locked centrally with cylinder lock.

**Colour:**

RAL 7035 light grey **powder-coated**.

**Note:**

When equipping the cabinet with drawers, check that the sum of the individual drawer front heights adds up to the usable cabinet height. When fitting out cabinet variants with doors, take into account the usable height for drawers in the casing.

**Only drawers No. 927805 can be fitted to the casing!**

Do not slide these under workstations with electric height adjustment No. 920301 – 920316.

**Technical description**

Wheel Ø	125 mm
Width	600 mm
Number of castors with parking brake	2
maximum load capacity	600 kg
Weight	32.5 kg
Depth	650 mm
Usable height	625 mm
Treadless tyres	yes
ComfortClose	no
Number of doors	0
Height	900 mm
with anti-roll lip	yes
Number of drawers	0
Electronic locking system can be retrofitted	yes
Number of fixed wheels without parking brake	2
Version	wheeled
Version	for individual configuration
Casing open at the top	no
Number of pull-out shelves	0
Usable height for drawers	625 mm
Material thickness	1 mm
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workshop mobile drawer unit

