

Garant GRIDLINE

Drawer, 20×20G, Drawer front height: 250mm**Order data**

Order number	927800 250
GTIN	4062406111854
Item class	9GG

Description**Version:**

100% full extension drawers in sturdy steel construction, with differential runners and 75 kg load capacity. Aluminium handles with labelling strips that can be exchanged and rewritten. New type of drawer concept for optimum equipment with dividing material.

Suitable for:

All 24G casings.

Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Usable height	225 mm
Weight	12 kg
Drawer/pull-out shelf load capacity	75 kg
Front height	250 mm
Drawer usable area in G	20×20
Usable depth in G	20
Usable width in G	20
Application range	Workbench casing

Usable width	500 mm
Usable depth	500 mm
with individual drawer release system	no
Material thickness	1 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	20×20G
Type of product	Drawer