

Garant GRIDLINE

Drawer with one-handed individual drawer release system, 20×20G, Drawer front height: 300mm



Order data

| | |
|--------------|---------------|
| Order number | 927805 300 |
| GTIN | 4062406111946 |
| Item class | 9GG |

Description

Version:

100% full extension drawers in sturdy steel construction, with differential runners and 75 kg load capacity. Aluminium handles with labelling strips that can be exchanged and rewritten. New type of drawer concept for optimum equipment with dividing material.

Drawers with **one-handed individual drawer release system** prevents the opening of drawers during transport. For fitting to mobile workbenches and casings.

Suitable for:

All 24G casings.

Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

| | |
|-------------------------------------|----------|
| Individual drawer release system | One-hand |
| Front height | 300 mm |
| Drawer usable area in G | 20×20 |
| Drawer/pull-out shelf load capacity | 75 kg |
| Usable height | 275 mm |
| Weight | 13 kg |

| | |
|--|---|
| Usable width in G | 20 |
| Usable depth in G | 20 |
| Application range | Assembly trolley |
| Usable width | 500 mm |
| Usable depth | 500 mm |
| with individual drawer release system | yes |
| Material thickness | 1 mm |
| Drawer runner extension (partial/full extension) | 100 % |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Drawer usable width × usable depth in G | 20×20G |
| Type of product | Drawer |