

Garant GRIDLINE

**24G casing, mobile, for individual configuration with drawers, 20×20G,
Height of the housing: 500mm****Order data**

Order number	927730 500
GTIN	4062406111762
Item class	9GG

Description**Version:**

24G casing, mobile, for individual configuration with drawers in sturdy steel construction. Covering with a ribbed rubber mat, raised edge and 2-component Haptoprene® push handles. With 2 each ball-bearing fixed wheels and castors, (castors with brakes for the wheels and the castor heads) Ø 125 mm, with treadless polyurethane tyres, minimum rolling resistance, low noise and fibre shields.

Can be locked centrally with cylinder lock.

Colour:

RAL 7035 light grey **powder-coated**.

Note:

When equipping the cabinet with drawers, check that the sum of the individual drawer front heights adds up to the usable cabinet height. When fitting out cabinet variants with doors, take into account the usable height for drawers in the casing.

Only drawers No. 927805 can be fitted to the casing!

Do not slide these under workstations with electric height adjustment No. 920301 – 920316.

Technical description

Wheel Ø	125 mm
Treadless tyres	yes
Depth	650 mm
Number of castors with parking brake	2
Electronic locking system can be retrofitted	yes
Height	700 mm
with anti-roll lip	yes
Number of doors	0
Usable height	425 mm
Number of drawers	0
maximum load capacity	600 kg
Weight	28.5 kg
ComfortClose	no
Number of fixed wheels without parking brake	2
Width	600 mm
Version	wheeled
Version	for individual configuration
Usable height for drawers	425 mm
Number of pull-out shelves	0
Casing open at the top	no
Material thickness	1 mm
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Workshop mobile drawer unit

