

Garant GRIDLINE

Drawer with one-handed individual drawer release system, 20×20G, Drawer front height: 250mm**Order data**

Order number	927805 250
GTIN	4062406111939
Item class	9GG

Description**Version:**

100% full extension drawers in sturdy steel construction, with differential runners and 75 kg load capacity. Aluminium handles with labelling strips that can be exchanged and rewritten. New type of drawer concept for optimum equipment with dividing material.

Drawers with **one-handed individual drawer release system** prevents the opening of drawers during transport. For fitting to mobile workbenches and casings.

Suitable for:

All 24G casings.

Colour:

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Technical description

Drawer usable area in G	20×20
Usable height	225 mm
Drawer/pull-out shelf load capacity	75 kg
Front height	250 mm
Individual drawer release system	One-hand
Weight	12 kg

Usable depth in G	20
Usable width in G	20
Application range	Assembly trolley
Usable width	500 mm
Usable depth	500 mm
with individual drawer release system	yes
Material thickness	1 mm
Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	20×20G
Type of product	Drawer