

Garant GRIDLINE

Chemicals storage cabinet with plain sheet metal swing doors, Height mm / number of containment trays: 2000/4**Order data**

Order number	980091 2000/4
GTIN	4062406112509
Item class	91U

Description**Version:**

Doors have ventilation slots at the sides and can be locked by slide handle with a **cylinder lock**. Galvanised containment tray to **StawaR** with welded leak-proof joints. Load capacity 100 kg. Height adjustable at 25 mm intervals. Drip catch volume 20 litres (20 mm below the lip of the tray).

Application:

Secure and correct storage of pesticides, toxic and water-hazardous chemicals in working rooms according to regulations.

Standard:

Übereinstimmungserklärung (ÜHP) gemäß Bauregelliste laufende Nummer 15.22 DIBT nach Richtlinie der StawaR (Stahlwannenrichtlinie).

Colour:

Standard ex stock – body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

Cabinet is not suitable for storage of flammable liquids! Storage to WHG § 19. Trays according to ÜHP in accordance with the Building Regulations List to the StawaR (Steel Tray Regulations). According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Width	1000 mm
Depth	500 mm
Number of containment trays	4
Cabinet fronts	Plain sheet metal swing doors with ventilation slots
Weight	135 kg
Usable height	1860 mm
Height	2000 mm
Material thickness	0.9 mm
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Cabinet housing internal load capacity	1000 kg
Door opening angle	225 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Chemicals storage cabinet

Accessories

Slide handle for GridLine Type GP11	914226 GP11
Drip tray cabinet / compartment width 1000 mm	980096 1000