


**Garant****Support columns, Height: 962mm****Order data**

Order number	928010 962
GTIN	4062406112240
Item class	91P

**Description****Version:**

Made of sturdy sheet metal. Barrier-free working area as no stabilising plate required. Insertion slots at 50 mm intervals on the front face, threaded sockets on the front and inner faces for holding other modules such as perforated panels, storage shelves etc. Support columns with side openings for cable routing. Supplied in pairs.

**Suitable for:**

Perforated sheet steel back panels 2 pc. No. 928070 or No. 928071.

**Colour:**

RAL 7035 light grey **powder coated**.

**Note:**

When using media tracks please also order the media module No. 928460 size CUT/OUT.  
Suitable for mounting support arm brackets.

**Technical description**

Weight	6 kg
Width	40 mm

Depth	100 mm
maximum load capacity	50 kg
maximum number of perforated panels	2 × No. 928070 or No. 928071
Height	962 mm
Material thickness	1 mm
Height adjustment interval	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Support column

## Accessories

Cross brace Length 1000 mm	928050 1000
Multifix bin Length mm / no. of containers 2000/19	928235 2000/19
Media module for support columns Module type CUT/OUT	928460 CUT/OUT
Media module for support columns Module type CH250/ONOF	928460 CH250/ONOF
Multifix bin Length mm / no. of containers 1500/14	928235 1500/14
Media module for support columns Module type DE250V/2	928460 DE250V/2
Support arm bracket Length 1500 mm	928055 1500
Multifix rail open storage bins Length mm / Type 2000/AB1	928230 2000/AB1
Perforated panel double-sided suitable for type 1500	928071 1500
Storage shelf with lighting suitable for type 2000	928140 2000
Media track with 4 sockets 250V suitable for type 1000	928443 1000
Multifix suitable for type 1000	928201 1000
Support arm bracket Length 1000 mm	928056 1000
Media module for support columns Module type FR250V/2	928460 FR250V/2
Shelf with steel hoops suitable for type 1500	928145 1500
Storage shelf of sheet metal 200 mm deep suitable for type 2000	928130 2000

Multimedia swivel arm with notebook holder Number of joints 2	928275 2
Drawing holder with organisation magnets suitable for type 1000	928211 1000
Storage shelf with lighting suitable for type 1000	928140 1000
Multifix bin Length mm / no. of containers 2000/13	928235 2000/13
Multimedia swivel arm with multi-function mounting Number of joints 1	928270 1
Viewing window suitable for type 2000	928090 2000
Swivel arm Number of joints 2	928170 2
Media module for support columns Module type OUT/ONOFF	928460 OUT/ONOFF
Perforated panel with brush strip suitable for type 1000	928111 1000
Multifix rail open storage bins Length mm / Type 1000/AB1	928230 1000/AB1
Media module for support columns Module type DK250/ONOF	928460 DK250/ONOF
Perforated panel single-sided suitable for type 2000	928070 2000
Media track with 2 sockets 250V suitable for type 1500	928442 1500
Support arm bracket Length 2000 mm	928056 2000
Storage shelf of sheet metal 300 mm deep suitable for type 1000	928131 1000
Media module for support columns Module type DE250/ONOF	928460 DE250/ONOF
Media track with 4 sockets 250V + On/Off suitable for type 1000	928444 1000
Perforated panel single-sided suitable for type 1000	928070 1000
Media track with 4 sockets 250V suitable for type 1500	928443 1500
Media module for support columns Module type ON/OFF	928460 ON/OFF
Multifix rail open storage bins Length mm / Type 1000/AA1	928230 1000/AA1
Multifix rail open storage bins Length mm / Type 1500/AB1	928230 1500/AB1
Storage shelf of sheet metal 300 mm deep suitable for type 1500	928131 1500

Multifix bin Length mm / no. of containers 1500/9	928235 1500/9
Media trackwith 4 sockets 250V suitable for type 2000	928443 2000
Multifix suitable for type 2000	928201 2000
Multifix with Easyfix magnetic clip suitable for type 1500	928206 1500
Multifix rail open storage bins Length mm / Type 1500/AA1	928230 1500/AA1
Media trackwith 2 sockets 250V suitable for type 2000	928442 2000
Perforated panel with brush strip suitable for type 2000	928111 2000
Media trackfor individual configuration suitable for type 1500	928441 1500
Perforated panel with brush strip suitable for type 1500	928111 1500
Support arm bracket Length 2000 mm	928055 2000
Cross brace Length 1500 mm	928050 1500
Multifix with Easyfix magnetic clip suitable for type 2000	928206 2000
Media trackwith 4 sockets 250V + On/Off suitable for type 1500	928444 1500
Perforated paneldouble-sided suitable for type 1000	928071 1000
Viewing window suitable for type 1000	928090 1000
Multimedia swivel arm with multi-function mounting Number of joints 2	928270 2
Support arm bracket Length 1500 mm	928056 1500
Viewing window suitable for type 1500	928090 1500
Shelf with steel hoops suitable for type 1000	928145 1000
Media trackwith 4 sockets 250V + On/Off suitable for type 2000	928444 2000
Perforated panelsingle-sided suitable for type 1500	928070 1500
Multifix bin Length mm / no. of containers 1000/9	928235 1000/9
Multifix suitable for type 1500	928201 1500
Cross brace Length 2000 mm	928050 2000
Storage shelf of sheet metal200 mm deep suitable for type 1000	928130 1000
Multifix bin Length mm / no. of containers 1000/6	928235 1000/6

Media module for support columns Module type DK250V/2	928460 DK250V/2
Drawing holderwith organisation magnets suitable for type 1500	928211 1500
Support arm bracket Length 1000 mm	928055 1000
Multifix with Easyfix magnetic clip suitable for type 1000	928206 1000
Media module for support columns Module type FR250/ ONOF	928460 FR250/ONOF
Storage shelf with lighting suitable for type 1500	928140 1500
Shelf with steel hoops suitable for type 2000	928145 2000
Drawing holderwith organisation magnets suitable for type 2000	928211 2000
Perforated panel single-sided suitable for type 500	928070 500
Media module for support columns Module type CH250V/2	928460 CH250V/2
Storage shelf of sheet metal 300 mm deep suitable for type 2000	928131 2000
Swivel arm Number of joints 1	928170 1
Media trackfor individual configuration suitable for type 2000	928441 2000
Multifix rail open storage bins Length mm / Type 2000/AA1	928230 2000/AA1
Media trackfor individual configuration suitable for type 1000	928441 1000
Media trackwith 2 sockets 250V suitable for type 1000	928442 1000
Storage shelf of sheet metal 200 mm deep suitable for type 1500	928130 1500
Perforated panel double-sided suitable for type 2000	928071 2000
LED lighting unit fixed laterally Power consumption 15 W	928620 15