

Garant**Support columns, Height: 200mm****Order data**

Order number	928010 200
GTIN	4062406112226
Item class	91P

Description**Version:**

Made of sturdy sheet metal. Barrier-free working area as no stabilising plate required. Insertion slots at 50 mm intervals on the front face, threaded sockets on the front and inner faces for holding other modules such as perforated panels, storage shelves etc. Support columns with side openings for cable routing. Supplied in pairs.

Colour:

RAL 7035 light grey **powder coated**.

Note:

Suitable only for media track, storage shelf and Multifix rail. Installation of media module No. 928460 not possible.

Support arm brackets and cross braces cannot be mounted.

Technical description

Weight	1.2 kg
Width	40 mm
Depth	100 mm

maximum load capacity	50 kg
Height	200 mm
Material thickness	1 mm
Height adjustment interval	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Support column

Accessories

Multifix with Easyfix magnetic clip suitable for type 1500	928206 1500
Shelf with steel hoops suitable for type 1000	928145 1000
Multifix bin Length mm / no. of containers 1000/9	928235 1000/9
Storage shelf of sheet metal 200 mm deep suitable for type 2000	928130 2000
Multifix bin Length mm / no. of containers 1500/9	928235 1500/9
Multifix bin Length mm / no. of containers 2000/13	928235 2000/13
Multifix suitable for type 1000	928201 1000
Multifix suitable for type 2000	928201 2000
Multifix rail open storage bins Length mm / Type 1500/AA1	928230 1500/AA1
Storage shelf of sheet metal 300 mm deep suitable for type 2000	928131 2000
Media track for individual configuration suitable for type 1500	928441 1500
Multifix with Easyfix magnetic clip suitable for type 1000	928206 1000
Storage shelf of sheet metal 300 mm deep suitable for type 1000	928131 1000
Swivel arm Number of joints 1	928170 1
Storage shelf of sheet metal 300 mm deep suitable for type 1500	928131 1500
Media track with 2 sockets 250V suitable for type 2000	928442 2000

Multifix rail open storage bins Length mm / Type 2000/AA1	928230 2000/AA1
Media trackwith 4 sockets 250V suitable for type 1500	928443 1500
Drawing holderwith organisation magnets suitable for type 1000	928211 1000
Media trackwith 4 sockets 250V suitable for type 2000	928443 2000
Drawing holderwith organisation magnets suitable for type 2000	928211 2000
Media trackwith 4 sockets 250V + On/Off suitable for type 1000	928444 1000
Multifix rail open storage bins Length mm / Type 1500/AB1	928230 1500/AB1
Multifix bin Length mm / no. of containers 1500/14	928235 1500/14
Swivel arm Number of joints 2	928170 2
Multifix rail open storage bins Length mm / Type 1000/AB1	928230 1000/AB1
Multifix bin Length mm / no. of containers 2000/19	928235 2000/19
Shelf with steel hoops suitable for type 2000	928145 2000
Multifix rail open storage bins Length mm / Type 2000/AB1	928230 2000/AB1
Storage shelf of sheet metal200 mm deep suitable for type 1000	928130 1000
Multifix rail open storage bins Length mm / Type 1000/AA1	928230 1000/AA1
Media trackwith 2 sockets 250V suitable for type 1000	928442 1000
Media trackfor individual configuration suitable for type 1000	928441 1000
Drawing holderwith organisation magnets suitable for type 1500	928211 1500
Storage shelf of sheet metal200 mm deep suitable for type 1500	928130 1500
Media trackfor individual configuration suitable for type 2000	928441 2000
Media trackwith 4 sockets 250V + On/Off suitable for type 2000	928444 2000
Multifix with Easyfix magnetic clip suitable for type 2000	928206 2000
Multifix bin Length mm / no. of containers 1000/6	928235 1000/6

Multifix suitable for type 1500	928201 1500
Shelf with steel hoops suitable for type 1500	928145 1500
Media track with 4 sockets 250V suitable for type 1000	928443 1000
Media track with 2 sockets 250V suitable for type 1500	928442 1500
Media track with 4 sockets 250V + On/Off suitable for type 1500	928444 1500
LED lighting unit fixed laterally Power consumption 15 W	928620 15