

**Garant****Support arm bracket, Depth 550 mm, Length: 1000mm****Order data**

Order number	928056 1000
GTIN	4062406112615
Item class	91P

**Description****Version:**

Sturdy sheet metal design. Fitted in pairs, to carry the lighting unit No. 928600, 928602, 928606 and equipment track No. 928250.

**Colour:**

RAL 7035 light grey **powder coated**.

**Note:**

Suitable only for support columns size 962 and 1362.

**Technical description**

maximum load capacity	50 kg
Height	60 mm
Weight	7 kg
Throat	450 mm
Length	1000 mm
Depth	550 mm
Width	1000 mm
Application range	Support columns
Design version	Steel hollow section construction
Material thickness	1.5 mm

Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Depth 550 mm
Type of product	Extension base

---

## Accessories

LED lighting unit with ON/OFF switch suitable for type 1000	928602 1000
LED lighting unit suitable for type 1000	928600 1000
TAMETO lighting unit suitable for type 1000	928608 1000
Equipment track with 2 runners Length 1000 mm	928250 1000