

Garant

Perforated rear panel (pair support columns + 2 perforated panels single-sided), Height 962 mm, suitable for type: 1500

**Order data**

Order number	928076 1500
GTIN	4062406113063
Item class	91P

Description**Version:**

Pair of support columns of steel hollow section 100×40×2 mm. **Insertion slots** at 50-mm intervals on the front face, together with **threaded sockets** on the front face to accept other modules / components. Perforated sheet metal panel between the columns.

Application:

For screwing to worktops of lengths 1000, 1500, and 2000 mm.

Supplied with:

Consisting of **1 pc.** pair support columns + **2 pcs.** perforated panel on one side. Suitable for mounting support arm brackets.

Colour:

RAL 7035 light grey **powder coated**.

Technical description

Height	962 mm
suitable for type	1500 mm

Safe working load	200 kg
Perforated panel version	single-sided
Design version	Steel hollow section construction
Material thickness	1 mm
Hoffmann perforated panel grid interval	9×9 mm
Height adjustment interval	50 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Height 962 mm
Type of product	Perforated rear panel

Accessories

Connector for support column Type 1	938027 1
Connector for support column Type 2	938027 2
Perforated panelsingle-sided suitable for type 1500	928070 1500
Support columns Height 962 mm	928010 962