

Garant**Perforated panel with brush strip, suitable for type: 2000****Order data**

Order number	928111 2000
GTIN	4062406113186
Item class	91P

Description**Version:**

Perforated panel as described under No. 928070, including brush strip for feeding through cables from the rear. For bolting between the support columns No. 928010, in materials supply trolley No. 918590 and for divider walls No. 955430 and 955431. 2 centre ribs

Colour:

RAL 7035 light grey **powder coated**.

Technical description

Width	1920 mm
Weight	12 kg
suitable for type	2000 mm
Height	481 mm
Depth	25 mm
Perforated panel version	single-sided
Perforated panel version	with brush strip
Safe working load	100 kg
Material thickness	1.2 mm
Hoffmann perforated panel grid interval	9×9 mm

Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Perforated rear panel

Accessories

Support column for hooking into perforated panel Height 481 mm	928060 481
Multimedia swivel arm with notebook holder Number of joints 2	928275 2
Multifix suitable for type 1000	928201 1000
Multifix suitable for type 1500	928201 1500
Multifix suitable for type 500	928201 500
Multimedia swivel arm with multi-function mounting Number of joints 1	928270 1
Multimedia swivel arm with multi-function mounting Number of joints 2	928270 2
Multifix suitable for type 300	928201 300