

Garant**Storage shelf of sheet metal 300 mm deep, suitable for type: 1000****Order data**

Order number	928131 1000
GTIN	4062406113223
Item class	91P

Description**NOTE: Colour selection possible****Version:**

Made of sheet metal, with anti-roll lip on 3 sides. Front face angled. Can be fitted with the edge facing upwards or downwards. **Range of depth adjustment 110 mm.**

Can be locked **horizontally at 90°** and **inclined at 110°**.

Suitable for :

Installation by **mounting on** support columns, roller cabinet No. 918590 (size 1000).

Colour:

RAL 7035 light grey **powder coated**.

Note:

The shelves can be fitted with open storage bins, which can be found in section 96.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Width: 920 mm

Usable width: 880 mm

Usable depth: 300 mm

Installation height: 80 mm

Depth adjustment range: 110 mm

Technical description

Usable width	880 mm
Depth adjustment range	110 mm
suitable for type	1000
Usable depth	300 mm
Installation height	80 mm

Width	920 mm
Inclination angle	90 °
Inclination angle	110 °
Storage shelf version	Standard
Material thickness	1.5 mm
Shelf load capacity / maximum distributed shelf load (on metal)	25 kg
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Storage shelf

Accessories

Small parts storage bin Height mm / type 67/1	928137 67/1
Small parts storage bin Height mm / type 67/3	928137 67/3
Small parts storage bin Height mm / type 41/2	928137 41/2
Small parts storage bin Height mm / type 41/1	928137 41/1
Small parts storage bin Height mm / type 67/2	928137 67/2
Small parts storage bin Height mm / type 41/3	928137 41/3