

Garant
Storage shelf of sheet metal 300 mm deep, suitable for type: 1500

Order data

Order number	928131 1500
GTIN	4062406113230
Item class	91P

Description
Version:

Made of sheet metal, with raised edge on 3 sides. Front face angled. Can be fitted with the edge facing upwards or downwards. **Range of depth adjustment 110 mm.**

Can be locked **horizontally at 90°** and **inclined at 110°**.

Suitable for:

Installation by **mounting** on the support columns No. 928010, materials supply trolley No. 918590 (size 1000) and divider walls No. 955430 and 955431.

Colour:

RAL 7035 light grey **powder coated**.

Note:

The shelves can be fitted with open storage bins, which can be found in section 96.

Technical description

Depth adjustment range	110 mm
Usable depth	300 mm
suitable for type	1500
Width	1420 mm
Installation height	80 mm
Usable width	1380 mm
Inclination angle	90 degrees
Inclination angle	110 degrees
Storage shelf version	Standard

Material thickness	1.5 mm
Shelf load capacity / maximum distributed shelf load (on metal)	25 kg
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Storage shelf