

**Garant**
**Storage shelf of sheet metal 200 mm deep, suitable for type: 1000**

**Order data**

Order number	928130 1000
GTIN	4062406113193
Item class	91P

**Description**
**Version:**

Made of sheet metal, with raised edge on 3 sides. Front face angled. Can be fitted with the edge facing upwards or downwards. **Range of depth adjustment 110 mm.**

Can be locked **horizontally at 90°** and **inclined at 110°**.

**Suitable for:**

Installation by **mounting** on the support columns No. 928010, materials supply trolley No. 918590 (size 1000) and divider walls No. 955430 and 955431.

**Colour:**

RAL 7035 light grey **powder coated**.

**Note:**

If 1 shelf is mounted to the front and 1 shelf to the rear of the support columns the shelf space is doubled. The shelves can be fitted with open storage bins, which can be found in section 96.

**Technical description**

suitable for type	1000
Usable depth	200 mm
Usable width	880 mm
Installation height	80 mm
Depth adjustment range	40 mm
Width	920 mm
Inclination angle	90 degrees
Inclination angle	110 degrees

Storage shelf version	Standard
Material thickness	1.5 mm
Shelf load capacity / maximum distributed shelf load (on metal)	25 kg
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Storage shelf