

**Garant****Storage shelf with lighting, suitable for type: 1500****Order data**

Order number	928140 1500
GTIN	4062406113339
Item class	91P

**Description****Version:**

Storage shelf as described under No. 928131. With integral tiltable LED lighting (arrangement as for No. 928600 with On/Off switch) underneath the storage shelf.

**Colour:**

Light grey RAL 7035, **powder-coated**, lampholder silver.

**Note:**

The lamp below the storage shelf incorporates built-in LED bulbs. The light source (LED bulbs) can be exchanged by the manufacturer. The operating unit (mains adapter and cable) can be replaced by the manufacturer.

**Technical description**

Illumination	2520 lm
Width	1420 mm
Colour temperature	4000 K
Usable depth	300 mm
Usable width	1380 mm
Power consumption	27 W
LED technology	yes
suitable for type	1500
Installation height	80 mm
On/Off switch	yes

Plug type, input	GST plug-in system
Nominal voltage	250 V
Storage shelf version	with lighting
Material thickness	1.5 mm
Shelf load capacity / maximum distributed shelf load (on metal)	25 kg
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Storage shelf