

Garant**Storage shelf with lighting, suitable for type: 1000****Order data**

Order number	928140 1000
GTIN	4062406113322
Item class	91P

Description**Version:**

Storage shelf as described under No. 928131. With integral tiltable LED lighting (arrangement as for No. 928600 with On/Off switch) underneath the storage shelf.

Colour:

Light grey RAL 7035, **powder-coated**, lampholder silver.

Note:

The lamp below the storage shelf incorporates built-in LED bulbs. The light source (LED bulbs) can be exchanged by the manufacturer. The operating unit (mains adapter and cable) can be replaced by the manufacturer.

Technical description

Installation height	80 mm
LED technology	yes
Power consumption	18 W
Usable depth	300 mm
Width	920 mm
Colour temperature	4000 K
suitable for type	1000
Usable width	880 mm
Illumination	1890 lm
Plug type, input	GST plug-in system

Nominal voltage	250 V
On/Off switch	yes
Storage shelf version	with lighting
Material thickness	1.5 mm
Shelf load capacity / maximum distributed shelf load (on metal)	25 kg
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Storage shelf