

Garant**Plug-in basic rack, Depth 400 mm, Height: 1000mm****Order data**

| | |
|--------------|---------------|
| Order number | 990201 1000 |
| GTIN | 4062406113575 |
| Item class | 91I |

Description**Version:**

Sturdy column frame of rectangular columns (50×25×1.25mm) with slots at intervals of 40 mm for mounting cross beams / shelves. Column frame with plastic end caps. No tools required for assembly. The high lateral stability eliminates the need for diagonal braces. Storage shelves of galvanised sheet metal.

Colour:

Column frames RAL 7016 anthracite **powder-coated**. Pairs of cross beams are **always** RAL 7016 anthracite grey.

Note:

- **The 500 mm deep shelves are dimensionally compatible with GridLine cabinets and can be combined with them in any way.**
- **Individual parts and accessories for storage shelves and racks can also be found in our eShop under No. 990271 – 990370.**
- **To ensure the stability of the racking, measures to prevent tipping are necessary where the height to depth ratio is greater than 5:1.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

Technical description

| | |
|---|--|
| Storage shelf clear width | 900 mm |
| Type of shelf fastening | Cross rail |
| Number of shelves | 3 |
| Shelf width | 946 mm |
| Number of profile frames | 2 |
| Rack depth | 400 mm |
| maximum bay load | 900 kg |
| Assembled size basic rack width | 1000 mm |
| Storage shelf depth | 400 mm |
| Rack height | 1000 mm |
| Rack installation | Basic rack |
| Shelf load capacity / maximum distributed shelf load (on metal) | 120 kg |
| Shelf thickness | 38 mm |
| Height adjustment interval | 40 mm |
| Colour selection | RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003 |
| Product name attribute | Depth 400 mm |
| Type of product | Storage shelf |

Accessories

Storage shelf, galvanised with pair of cross beams suitable for racking depth 400 mm

990320 400