

Garant**Corner connection rack with 1 corner column, Depth 500 mm, Height: 2400mm****Order data**

Order number	990246 2400
GTIN	4062406114206
Item class	911

Description**Version:**

Sturdy corner column made of rectangular columns (50×25×1.25 mm) with slots at intervals of 40 mm for mounting cross beams / shelves. Column frame with plastic end caps. No tools required for assembly. The high lateral stability eliminates the need for diagonal braces. Storage shelves made from galvanised sheet metal.

Supplied with:

Corner column, corner shelf (see the respective size for the quantity). 1 pc. corner column, 5 pcs. corner storage shelves.

Colour:

Column frames RAL 7016 anthracite **powder-coated**. Pairs of cross beams are **always** RAL 7016 anthracite grey.

Note:

A corner connection can only be used in combination with 2 basic racks No. 990201 or No. 990211.

Technical description

Rack height	2400 mm
maximum bay load	900 kg

Number of shelves	5
Storage shelf depth	975 mm
Shelf width	975 mm
Storage shelf front edge (dimension A)	636 mm
suitable for connection to racking depth	500 mm
The rack requires connecting racks for assembly	yes
Unique corner solution	no
Customer assembly	yes
Storage shelf depth (dimension B)	972 mm
Shelf load capacity / maximum distributed shelf load (on metal)	120 kg
Shelf thickness	38 mm
Height adjustment interval	40 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Depth 500 mm
Type of product	Corner connecting racks

Accessories

Corner shelf, galvanised with cross beams suitable for connection to racking depth 500 mm	990370 500
---	------------