

**Garant****Plug-in extension rack, Depth 500 mm, Height: 2000mm****Order data**

Order number	990216 2000
GTIN	4062406114299
Item class	911

**Description****Version:**

Sturdy column frame of rectangular columns (50×25×1.25mm) with slots at intervals of 40 mm for mounting cross beams / shelves. Column frame with plastic end caps. No tools required for assembly. The high lateral stability eliminates the need for diagonal braces. Storage shelves of galvanised sheet metal.

**Colour:**

Column frames RAL 7016 anthracite **powder-coated**. Pairs of cross beams are **always** RAL 7016 anthracite grey.

**Note:**

- **The 500 mm deep shelves are dimensionally compatible with GridLine cabinets and can be combined with them in any way.**
- **Individual parts and accessories for storage shelves and racks can also be found in our eShop under No. 990271 – 990370.**
- **To ensure the stability of the racking, measures to prevent tipping are necessary where the height to depth ratio is greater than 5:1.**
- **Supplied for self-assembly, saving freight costs. Delivered unassembled.**

**Technical description**

Storage shelf depth	500 mm
Rack installation	Extension rack
Storage shelf clear width	900 mm
Type of shelf fastening	Cross rail
Number of profile frames	1
Number of shelves	4
Shelf width	946 mm
Rack depth	500 mm
Assembled size add-on rack width	975 mm
Rack height	2000 mm
maximum bay load	900 kg
Shelf load capacity / maximum distributed shelf load (on metal)	120 kg
Shelf thickness	38 mm
Height adjustment interval	40 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Depth 500 mm
Type of product	Storage shelf

## Accessories

Storage shelf, galvanised with pair of cross beams suitable for racking depth 500 mm

990320 500