

Garant**Column frame with sheet metal cladding, Depth 500 mm, Height: 1000mm****Order data**

Order number	990296 1000
GTIN	4062406114442
Item class	911

Description**Version:**

With slots at 40 mm intervals and plastic end caps at both ends. Perforated sheet metal panels prevent access to the shelves from the side.

Application:

For basic and extension racks No. 990201 – 990216, for use as intermediate frame or end frame.

Colour:

Anthracite RAL 7016 **powder-coated.**

Technical description

Can be used as a partition	yes
Width	500 mm
Height	1000 mm
suitable for racking height	1000 mm
suitable for racking depth	500 mm
Customer assembly	yes

Shelf adaption	1-sided
suitable for storage shelf racking	yes
Rack height	1000 mm
Hoffmann perforated panel grid interval	9×9 mm
Height adjustment interval	40 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Depth 500 mm
Type of product	Column frame

Accessories

Compensation shims,Set of 10 pieces	990398
2-piece bracket set, for securing to the floor	990399