

Garant**Column frame with sheet metal panel, Depth 500 mm, Height: 1200mm****Order data**

Order number	990296 1200
GTIN	4062406114473
Item class	91I

Description**Version:**

With slots at 40 mm intervals and plastic end caps at both ends. Perforated sheet metal panel prevents access to the shelves from the side.

Application:

For basic and extension racks No. 990201 – 990216, for use as intermediate frame or end frame.

Colour:

Anthracite RAL 7016 **powder-coated**.

Technical description

suitable for racking depth	500 mm
Width	500 mm
Shelf adaption	1-sided
Can be used as a partition	yes
Customer assembly	yes
suitable for racking height	1200 mm

suitable for storage shelf racking	yes
Rack height	1200 mm
Height	1200 mm
Hoffmann perforated panel grid interval	9×9 mm
Height adjustment interval	40 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Depth 500 mm
Type of product	Column frame

Accessories

2-piece bracket set, for securing to the floor	990399
Compensation shims,Set of 10 pieces	990398