

Garant**Column frame with sheet metal cladding, Depth 400 mm, Height: 2400mm****Order data**

Order number	990291 2400
GTIN	4062406114480
Item class	91I

Description**Version:**

With slots at 40 mm intervals and plastic end caps at both ends. Perforated sheet metal panels prevent access to the shelves from the side.

Application:

For basic and extension racks No. 990201 – 990216, for use as intermediate frame or end frame.

Colour:

Anthracite RAL 7016 **powder-coated.**

Technical description

suitable for racking depth	400 mm
Height	2400 mm
Width	400 mm
Can be used as a partition	yes
suitable for storage shelf racking	yes
Shelf adaption	1-sided

suitable for racking height	2400 mm
Customer assembly	yes
Rack height	2400 mm
Hoffmann perforated panel grid interval	9×9 mm
Height adjustment interval	40 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Depth 400 mm
Type of product	Column frame

Accessories

Compensation shims,Set of 10 pieces	990398
2-piece bracket set, for securing to the floor	990399