

**Garant****Column frame with sheet metal panel, Depth 400 mm, Height: 800mm****Order data**

Order number	990291 800
GTIN	4062406114404
Item class	91I

**Description****Version:**

With slots at 40 mm intervals and plastic end caps at both ends. Perforated sheet metal panel prevents access to the shelves from the side.

**Application:**

For basic and extension racks No. 990201 – 990216, for use as intermediate frame or end frame.

**Colour:**

Anthracite RAL 7016 **powder-coated**.

**Technical description**

Shelf adaption	1-sided
Height	800 mm
Customer assembly	yes
Can be used as a partition	yes
Width	400 mm
suitable for storage shelf racking	yes

suitable for racking depth	400 mm
Rack height	800 mm
suitable for racking height	800 mm
Hoffmann perforated panel grid interval	9×9 mm
Height adjustment interval	40 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Depth 400 mm
Type of product	Column frame

---

## Accessories

2-piece bracket set, for securing to the floor	990399
Compensation shims, Set of 10 pieces	990398