

**Garant****Column frame with sheet metal panel, Depth 400 mm, Height: 1000mm****Order data**

Order number	990291 1000
GTIN	4062406114411
Item class	91I

**Description****Version:**

With slots at 40 mm intervals and plastic end caps at both ends. Perforated sheet metal panel prevents access to the shelves from the side.

**Application:**

For basic and extension racks No. 990201 – 990216, for use as intermediate frame or end frame.

**Colour:**

Anthracite RAL 7016 **powder-coated**.

**Technical description**

Customer assembly	yes
Rack height	1000 mm
suitable for storage shelf racking	yes
Height	1000 mm
Width	400 mm
suitable for racking height	1000 mm

Can be used as a partition	yes
Shelf adaption	on 1 side
suitable for racking depth	400 mm
Hoffmann perforated panel grid interval	9×9 mm
Height adjustment interval	40 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Depth 400 mm
Type of product	Column frame

---

## Accessories

2-piece bracket set, for securing to the floor	990399
Compensation shims, Set of 10 pieces	990398