

Garant**Column frame with sheet metal cladding, Depth 500 mm, Height: 2400mm****Order data**

Order number	990296 2400
GTIN	4062406114503
Item class	911

Description**Version:**

With slots at 40 mm intervals and plastic end caps at both ends. Perforated sheet metal panels prevent access to the shelves from the side.

Application:

For basic and extension racks No. 990201 – 990216, for use as intermediate frame or end frame.

Colour:

Anthracite RAL 7016 **powder-coated.**

Technical description

Can be used as a partition	yes
Rack height	2400 mm
suitable for storage shelf racking	yes
Height	2400 mm
Width	500 mm
Customer assembly	yes

Shelf adaption	1-sided
suitable for racking depth	500 mm
suitable for racking height	2400 mm
Hoffmann perforated panel grid interval	9×9 mm
Height adjustment interval	40 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	Depth 500 mm
Type of product	Column frame

Accessories

2-piece bracket set, for securing to the floor	990399
Compensation shims,Set of 10 pieces	990398