

Garant
Arbor 90°, cylindrical with IC short, Type: 29

Order data

Order number	239740 29
GTIN	4062406115760
Item class	23A

Description
Version:

Version suitable for NC with straight shank \varnothing for standard arbors especially in **hydraulic chucks** or **high precision collet chucks** for very high accuracy and process reliability.

Note:

Observe the mounting size of the holder and reaming heads. For further arbors see No. 210550 – 210582 and No. 212000.

Shank: DIN 6535 HA to h6

suitable for through hole \varnothing : 32.21 - 50 mm

suitable for blind hole \varnothing : 40.21 - 50 mm

Overall length L: 146 mm

Reach L_1 : 82.5 mm

Shank $\varnothing D_s$ h6: 32 mm

recommended tightening torque: 35 N·m

Technical description

suitable for through hole \varnothing	32.21 - 50 mm
suitable for blind hole \varnothing	40.21 - 50 mm
Shank $\varnothing D_s$ h6	32 mm
Reach L_1	82.5 mm
recommended tightening torque	35 N·m
Overall length L	146 mm
Series	TopCut

Through-coolant	yes
Shank	DIN 6535 HA to h6
Type of product	Threaded copy mill arbor