

**Garant**
**Arbor 90°, cylindrical with IC long, Type: 24**

**Order data**

Order number	239745 24
GTIN	4062406115777
Item class	23A

**Description**
**Version:**

Version suitable for NC with straight shank  $\varnothing$  for standard arbors especially in **hydraulic chucks** or **high precision collet chucks** for very high accuracy and process reliability.

**Note:**

Observe the mounting size of the holder and reaming heads. For further arbors see No. 210550 – 210582 and No. 212000.

Shank: DIN 6535 HA to h6

suitable for through hole  $\varnothing$ : 26.21 - 32.2 mm

suitable for blind hole  $\varnothing$ : 30.21 - 40.2 mm

Overall length L: 202 mm

Reach  $L_1$ : 144 mm

Shank  $\varnothing D_s$  h6: 25 mm

recommended tightening torque: 25 N·m

**Technical description**

recommended tightening torque	25 N·m
Shank $\varnothing D_s$ h6	25 mm
suitable for through hole $\varnothing$	26.21 - 32.2 mm
Reach $L_1$	144 mm
suitable for blind hole $\varnothing$	30.21 - 40.2 mm
Overall length L	202 mm
Series	TopCut

Through-coolant	yes
Shank	DIN 6535 HA to h6
Type of product	Threaded copy mill arbor