

Garant**ZeroClamp adapter for SK (DIN 69871) arbors, suitable for clamping pot Ø: 138mm****Order data**

Order number	360042 138
GTIN	4045197722829
Item class	310

Description**Version:**

The zero point clamping of the GARANT ZeroClamp system is an important function for modern production systems, especially in automated production. Thanks to a special contact interface, it ensures precise and reliable zero point repetition accuracy. The pneumatic clamping force of the system holds workpieces securely in the desired position, making it possible to change workpieces quickly and accurately without repositioning. This reduces the set-up effort and increases productivity. The zero point clamping of the GARANT ZeroClamp system is indispensable for efficient production processes. Find out more about the innovative technology from GARANT ZeroClamp and optimise your production.

Application:

Can be used horizontally and vertically. Clamping workpieces via an SK arbor (DIN 69871) (such as ER, OZ etc.). Clamping studs are bolted through the adapter from below to secure the arbor. Especially suitable for small, delicate or round workpieces.

Suitable for:

Clamping pots Ø 90, Ø 120 or Ø 138 mm with indexing hole.

Note:

Clamping stud No. 360025 size 14M12/90 for Ø 90 mm.

Clamping stud No. 360025 size 18M16 for Ø 120 mm.

Clamping stud No. 360025 size 18M16/138 for Ø 138 mm.

Must be ordered separately!

Technical description

Number of location holes for clamping studs	1
suitable for clamping pot \varnothing	138 mm
Installed height H	77 mm
Series	ZeroClamp
suitable for	SK40
Type of product	Pin vice

Accessories

ZeroClamp clamping stud with internal thread Type 18M16/138	360025 18M16/138
---	------------------