


Garant**ZeroClamp extension base with 200 pitch, Type: 12126****Order data**

Order number	360031 12126
GTIN	4045197722683
Item class	310

Description**Version:**

With 2 clamping pots. The zero point clamping of the GARANT ZeroClamp system is an important function for modern production systems, especially in automated production. Thanks to a special contact interface, it ensures precise and reliable zero point repetition accuracy. The pneumatic clamping force of the system holds workpieces securely in the desired position, making it possible to change workpieces quickly and accurately without repositioning. This reduces the set-up effort and increases productivity. The zero point clamping of the GARANT ZeroClamp system is indispensable for efficient production processes. Find out more about the innovative technology from GARANT ZeroClamp and optimise your production.

Suitable for:

For base plates with pitch 200.

Supplied with:

Including coupling plug and clamping stud No. 360025 size 18M16.

Optional extras:

Quick-release coupling No. 360019 size 10241 and size 10003.

Note:

Consoles with clamping pot dia. 138 mm are also available with self-locking clamping pots on request!

Technical description

Installed height H	150 mm
Number of clamping studs	2
Type	12126
Clamping pot Ø	120 mm
Series	ZeroClamp
Type of product	Extension base

Accessories

ZeroClamp quick-release coupling Type 10003	360019 10003
---	--------------