

Garant**LED lighting unit, suitable for type: 1000****Order data**

Order number	928600 1000
GTIN	4062406117443
Item class	91P

Description**Version:**

Lighting unit complete with lampholder and connecting cable for fitting to switch No. 928470 ON/OFF or 928460 ON/OFF (industrial plug). Maintenance-free LED technology with long working life. The energy-efficient light source is even, does not flicker or dazzle and has a balanced spectral distribution which allows good colour recognition and high definition of contours and contrasts. Colour temperature / light colour approx. 4000 K.

This lamp incorporates built-in LED bulbs. The bulbs cannot be changed within the lamp. LED lighting unit with silver casing of sheet metal and shade of PMMA.

Suitable for:

Support arm brackets No. 928055, 928056, 972086 and 972087.

Colour:

Body silver similar to RAL 9006.

Technical description

Depth	120 mm
Non-dazzle, flicker-free	yes
Lighting unit depth	30 mm
Lampholder length	850 mm
Length	920 mm
Series	Workstation
Illumination	1890 lm
Power consumption	27 W

Weight	3 kg
suitable for type	1000 mm
LED technology	yes
Colour temperature	4000 K
Power supply	Mains operated
On/Off switch	no
Plug type, input	GST plug-in system
Nominal voltage	250 V
Material thickness	1 mm
Type of product	Mounted light