

Garant**LED lighting unit, suitable for type: 2000****Order data**

Order number	928600 2000
GTIN	4062406117467
Item class	91P

Description**Version:**

Lighting unit complete with lampholder and connecting cable for fitting to switch No. 928470 ON/OFF or 928460 ON/OFF (industrial plug). Maintenance-free LED technology with long working life. The energy-efficient light source is even, does not flicker or dazzle and has a balanced spectral distribution which allows good colour recognition and high definition of contours and contrasts. Colour temperature / light colour approx. 4000 K.

This lamp incorporates built-in LED bulbs. The bulbs cannot be changed within the lamp. LED lighting unit with silver casing of sheet metal and shade of PMMA.

Suitable for:

Support arm brackets No. 928055, 928056, 972086 and 972087.

Colour:

Body silver similar to RAL 9006.

Technical description

Depth	120 mm
Power consumption	36 W
Illumination	2520 lm
suitable for type	2000 mm
Series	Workstation
LED technology	yes
Lighting unit depth	30 mm
Colour temperature	4000 K

Non-dazzle, flicker-free	yes
Length	1920 mm
Lampholder length	1110 mm
Weight	6 kg
Power supply	Mains operated
Plug type, input	GST plug-in system
Nominal voltage	250 V
On/Off switch	no
Material thickness	1 mm
Type of product	Mounted light