

**Garant**
**LED lighting unit with ON/OFF switch, suitable for type: 1500**

**Order data**

Order number	928602 1500
GTIN	4062406117481
Item class	91P

**Description**
**Version:**

Lighting unit complete with lampholder and connecting cable for fitting to switch No. 928470 ON/OFF or 928460 ON/OFF (industrial plug). Maintenance-free LED technology with long working life. The energy-efficient light source is even, does not flicker or dazzle and has a balanced spectral distribution which allows good colour recognition and high definition of contours and contrasts. Colour temperature / light colour approx. 4000 K.

This lamp incorporates built-in LED bulbs. The bulbs cannot be changed within the lamp. LED lighting unit with silver casing of sheet metal and shade of PMMA.

**Suitable for:**

Support arm brackets No. 928055, 928056, 972086 and 972087.

**Colour:**

Body silver similar to RAL 9006.

**Technical description**

Series	Workstation
Depth	120 mm
Number of on/off switches	1
Length	1420 mm
suitable for type	1500 mm
Power consumption	36 W
Lampholder length	1110 mm
Non-dazzle, flicker-free	yes

Lighting unit depth	30 mm
Colour temperature	4000 K
LED technology	yes
Weight	4 kg
Illumination	2520 lm
Power supply	Mains operated
On/Off switch	yes
Nominal voltage	250 V
Plug type, input	GST plug-in system
Material thickness	1 mm
Type of product	Mounted light