

Waldmann **TAMETO lighting unit, suitable for type: 1500****Order data**

Order number	928608 1500
GTIN	4013330060695
Item class	93L

Description**Version:**

Lighting unit complete with lampholder and connecting cable for fitting to switch No. 928470 ON/OFF or 928460 ON/OFF (industrial plug). Maintenance-free LED technology with long working life. The energy-efficient light source is even, does not flicker or dazzle and has a balanced spectral distribution which allows good colour recognition and high definition of contours and contrasts. Colour temperature / light colour approx. 4000 K.

This lamp incorporates built-in LED bulbs. The bulbs cannot be changed within the lamp. LED lighting unit with casing of unpainted anodised aluminium and black plastic. Dazzle prevention by a conical prismatic shade of PMMA. The lighting unit is steplessly dimmable and is protected against contamination by its sealed design. Connection by the industrial plug connector system for simple ladder cabling.

Function:

IP20: No protection against penetration by foreign bodies with $\varnothing < 12$ mm, however touching should be avoided, and no protection against water.

Suitable for:

Support arm brackets No. 928055, 928056, 972086 and 972087.

Technical description

Depth	187 mm
Length	1420 mm
steplessly dimmable	yes
Lighting unit depth	167 mm
Lampholder length	1190 mm
Colour temperature	4000 K

Non-dazzle, flicker-free	yes
Weight	4 kg
Power consumption	33 W
LED technology	yes
suitable for type	1500 mm
Illumination	3200 lm
Power supply	Mains operated
Nominal voltage	250 V
Plug type, input	GST plug-in system
IP Index of Protection	IP 20
On/Off switch	yes
Material thickness	1 mm
Type of product	Mounted light