

**Garant****LED lighting unit with ON/OFF switch, suitable for type: 1000****Order data**

Order number	928602 1000
GTIN	4062406117474
Item class	91P

**Description****Version:**

Lighting unit complete with lampholder and connecting cable for fitting to switch No. 928470 ON/OFF or 928460 ON/OFF (industrial plug). Maintenance-free LED technology with long working life. The energy-efficient light source is even, does not flicker or dazzle and has a balanced spectral distribution which allows good colour recognition and high definition of contours and contrasts. Colour temperature / light colour approx. 4000 K.

This lamp incorporates built-in LED bulbs. The bulbs cannot be changed within the lamp.

LED lighting unit with silver casing of sheet metal and shade of PMMA.

**Suitable for:**

Support arm brackets No. 928055, 928056, 972086 and 972087.

**Colour:**

Body silver similar to RAL 9006.

**Technical description**

Lighting unit depth	30 mm
Illumination	1890 lm
Weight	3 kg
Power consumption	27 W
Number of on/off switches	1
Depth	120 mm
LED technology	yes

Non-dazzle, flicker-free	yes
Length	920 mm
suitable for type	1000 mm
Lampholder length	850 mm
Colour temperature	4000 K
Series	Workstation
Power supply	Mains operated
Plug type, input	GST plug-in system
Nominal voltage	250 V
On/Off switch	yes
Material thickness	1 mm
Type of product	Mounted light