

Waldmann **Arm-mounted luminaire Taneo, Type: 47****Order data**

Order number	928655 47
GTIN	4013330055967
Item class	93L

Description**Version:**

Efficient high-quality LED technology, maintenance-free, providing flat, even illumination, non-dazzling and free of shadows. Film key pad with On/Off and dimming (stepless down to 10 %, with memory function). Casing of unpainted anodised aluminium. Cantilever arms with spring restraint and 3D head joint. Colour temperature neutral white at 4,000 K.

The lamp incorporates built-in LED bulbs. The light source (LED bulbs) can be exchanged by the manufacturer. The operating unit (mains adapter and cable) can be replaced by the customer. With 36 LEDs.

Supplied with:

Table clamp (0 - 70 mm span).

3.0m connection cable with Euro plug.

Technical description

Power supply	Mains-powered
Lamp body length	577 mm
Lamp body width	136 mm
Radius of movement of 3D jointed arm	180 degrees
Bulb	LED
Lamp body height	33 mm
Type of fastening	Table clamp

Light colour	neutral white K
Connection cable length	3 m
Power consumption	30 W
Dimmable lighting	stepless
Lamp replaceable	no
Nominal voltage	250 V
Colour temperature	4000 K
Overall height	1070 mm
Plug type, input	C
On/Off switch	yes
Type of product	Desk lamp / workstation lamp