

Waldmann **Arm-mounted luminaire Taneo, Type: 31****Order data**

Order number	928655 31
GTIN	4013330055943
Item class	93L

Description**Version:**

Efficient high-quality LED technology, maintenance-free, providing flat, even illumination, non-dazzling and free of shadows. Film key pad with On/Off and dimming (stepless down to 10 %, with memory function). Casing of unpainted anodised aluminium. Cantilever arms with spring restraint and 3D head joint. Colour temperature neutral white at 4,000 K.

The lamp incorporates built-in LED bulbs. The light source (LED bulbs) can be exchanged by the manufacturer. The operating unit (mains adapter and cable) can be replaced by the customer. With 24 LEDs.

Supplied with:

Table clamp (0 - 70 mm span).

3.0m connection cable with Euro plug.

Technical description

Connection cable length	3 m
Bulb	LED
Radius of movement of 3D jointed arm	180 degrees
Lamp body length	398 mm
Type of fastening	Table clamp
Power consumption	23 W
Dimmable lighting	stepless

Power supply	Mains-powered
Lamp body width	136 mm
Light colour	neutral white K
Lamp body height	33 mm
Lamp replaceable	no
Nominal voltage	250 V
Colour temperature	4000 K
Overall height	1070 mm
On/Off switch	yes
Plug type, input	C
Type of product	Desk lamp / workstation lamp