

Garant

Top-mounted cabinet, suitable for type: 1500



Order data

Order number	928700 1500
GTIN	4062406117627
Item class	91P

Description

NOTE: Colour selection possible

Version:

Cabinet body of sheet metal with **double rear wall** (dust protection). Sheet steel perforated panel with \square 9x9 mm holes at 37 mm pitch. Door swings forward horizontally to open. For attachment between support columns No. 928010.

Application:

Also suitable for wall mounting.

Colour:

Body RAL 7035 light grey,

doors RAL 7016 anthracite **powder-coated**.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Height: 481 mm

Width: 1420 mm

Depth: 250 mm

Usable height: 410 mm

Usable width: 1380 mm

Usable depth: 150 mm

Technical description

suitable for type	1500
Weight	38 kg
Usable height	410 mm

Safe working load	120 kg
Depth	250 mm
Width	1420 mm
Usable width	1380 mm
Usable depth	150 mm
Height	481 mm
Material thickness	1 mm
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Top-mounted cabinet for workbench

Accessories

Gas pressure spring suitable for size 1500	938016 1500
Slide handle for top-mounted cabinet without cylinder insert	914232