

Garant**Top-mounted cabinet, suitable for type: 2000****Order data**

Order number	928700 2000
GTIN	4062406117634
Item class	91P

Description**Version:**

Cabinet body of sheet metal with **double rear wall** (dust protection). Sheet steel perforated panel with \square 9×9 mm holes at 37 mm pitch. Door swings forward horizontally to open. For attachment between support columns No. 928010.

Application:

Also suitable for wall mounting.

Colour:

Body RAL 7035 light grey,
doors RAL 7016 anthracite **powder-coated**.

Technical description

Height	481 mm
Usable width	1880 mm
Width	1920 mm
suitable for type	2000
Usable height	410 mm
Usable depth	150 mm
Safe working load	100 kg
Weight	50 kg
Depth	250 mm

Material thickness	1 mm
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Add-on cabinet

Accessories

Gas pressure spring suitable for size 2000	938016 2000
--	-------------