

**Garant****CaraFin diamond polishing point, D3, Type: ZY0608****Order data**

Order number	551940 ZY0608
GTIN	4062406114565
Item class	51G

**Description****Version:**

**Polishing points** of **resilient PU material** coated on the outer face with diamond grit. The effectiveness of the bonded diamond grit is significantly greater than that achieved by loose diamond grit in polishing pastes.

**Application:**

Polishing work with very high flexibility and conformity to contours.

**Technical description**

Head Ø	6 mm
Shank Ø	3 mm
recommended circumferential speed	1 - 2 m/s
Head length	8 mm
Series	CaraFin
Grinding media	Diamond

Grinding medium code	D
Grit designation	Mirror finish
Product name attribute	D3
Type of product	Polishing points

## User data

	Suitability	$V_c$	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
Carbide (HM)	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		