

Garant**CaraFin diamond polishing point, D10, Type: ZY1610****Order data**

Order number	551941 ZY1610
GTIN	4062406117818
Item class	51G

Description**Version:**

Polishing points of **resilient PU material** coated on the outer face with diamond grit. The effectiveness of the bonded diamond grit is significantly greater than that achieved by loose diamond grit in polishing pastes.

Application:

Polishing work with very high flexibility and conformity to contours.

Technical description

Head Ø	16 mm
Shank Ø	6 mm
recommended circumferential speed	1 - 2 m/s
Head length	10 mm
Series	CaraFin
Grinding media	Diamond

Grinding medium code	D
Grit designation	Final polishing
Product name attribute	D10
Type of product	Polishing points

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
Carbide (HM)	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		