

**Workbench with 4 drawers and 1 swing door, Worktop length: 1500mm****Order data**

Order number	929510 1500
GTIN	4062406117771
Item class	92W

Description**Version:**

- **Worktop 40 mm thick, non-warping beech marine ply, finished with clear UV varnish.**
- **Frame - welded sheet metal.**
- **Drawers of sheet metal with low-friction rollers of Delrin.**
- **Sheet metal doors with plastic grips, opening angle 180° and self-closing hinges.**
- **Central cylinder lock with 2 keys.**

Fitted with:

Drawer front height (left): 180; 180; 180

Drawer front height (right) mm: 180

Door height (right): 360

Optional extras:

For suitable storage shelf see No. 929581.

Colour:

Body RAL 7035 light grey, fronts anthracite RAL 7016, **powder-coated, internal shelves and storage shelves on top galvanized.**

Note:

Other colours available for fronts: RAL 7035 light grey, RAL 5005 signal blue. No special paint finishes available.

Technical description

Weight	92 kg
--------	-------

Material of worktop	Beech marine ply
Number of drawers	4
Drawer usable width	490 mm
Door height (right)	360 mm
Support cabinet depth	630 mm
Workbench can be locked centrally	yes
Drawer usable depth	520 mm
Worktop depth	700 mm
Worktop thickness	40 mm
Support cabinet width	1200 mm
Worktop length	1500 mm
Surface worktop	clear varnished
Height	850 mm
Workbench for installation in a row	no – the worktop projection is too large
Workbench/desk load capacity - maximum distributed load (on wood)	700 kg
Material thickness	1.5 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	100 kg
Insert thickness	40 mm
Drawer runner extension (partial/full extension)	90 %
Door opening angle	180 degrees
Height adjustment	20 mm
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Workbench

Accessories

Barrel sleeve 225-010-9 without lock barrel

914202