

**Workbench with 3 drawers and 1 swing door, Worktop length: 1500mm****Order data**

Order number	929530 1500
GTIN	4062406117795
Item class	92W

Description**Version:**

- **Worktop 40 mm thick, non-warping beech marine ply, finished with clear UV varnish.**
- **Frame - welded sheet metal.**
- **Drawers of sheet metal with low-friction rollers of Delrin.**
- **Sheet metal doors with plastic grips, opening angle 180° and self-closing hinges.**
- **Central cylinder lock with 2 keys.**

Fitted with:

Drawer front height (left) mm: 180; 180; 180

Door height (right) mm: 540

Optional extras:

For suitable storage shelf see No. 929581.

Colour:

Body RAL 7035 light grey, fronts anthracite RAL 7016, **powder-coated, internal shelves and storage shelves on top galvanized.**

Note:

Other colours available for fronts: RAL 7035 light grey, RAL 5005 signal blue. No special paint finishes available.

Technical description

Material of worktop	Beech marine ply
Worktop depth	700 mm

Worktop length	1500 mm
Surface worktop	clear varnished
Support cabinet depth	630 mm
Workbench can be locked centrally	yes
Number of drawers	3
Support cabinet width	1200 mm
Drawer usable depth	520 mm
Workbench/desk load capacity - maximum distributed load (on wood)	700 kg
Drawer usable width	490 mm
Worktop thickness	40 mm
Workbench for installation in a row	no – the worktop projection is too large
Height	850 mm
Weight	80 kg
Door height (right)	540 mm
Material thickness	1.5 mm
Workbench height	850 mm
Drawer/pull-out shelf load capacity	100 kg
Insert thickness	40 mm
Drawer runner extension (partial/full extension)	90 %
Door opening angle	180 degrees
Height adjustment	20 mm
Cylinder lock	modular barrel
Colour selection	RAL 7035, RAL 7016, RAL 5005
Type of product	Workbench

Accessories

Barrel sleeve 225-010-9 without lock barrel

914202