

**Burr set 5 pieces, tooth profile INOX - coarse, Carbide, Number of burrs: 5****Order data**

Order number	547110 5
GTIN	4007220068816
Item class	55F

Description**Version:**

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. Outstanding chip formation and surface results, low heat input into the material (no tempering colouration). Shank Ø 6mm.
Assortment of burrs in the most popular shapes and sizes. Shank Ø 6 mm.

Application:

Optimised for use on **austenitic, rust-resistant and acid-resistant steels**, soft titanium alloys and non-ferrous metals.

Supplied with:

1 pc. each No. 547200 size A1225; C1225; D1210; G1225; F1225.

Technical description

Tooth type abbreviation	INOX
Toothing grit designation	coarse
Tool material	Carbide
Shank Ø	6 mm

Number of burrs	5
Type of product	Burr

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		

Accessories

BurrTooth profile INOX – coarse Type A1225	547200 A1225
BurrTooth profile INOX – coarse Type C1225	547200 C1225
BurrTooth profile INOX – coarse Type G1225	547200 G1225
BurrTooth profile INOX – coarse Type F1225	547200 F1225
BurrTooth profile INOX – coarse Type D1210	547200 D1210