

Garant GRIDLINE

Workbench, left side open, right side 4 drawers, Beech marine ply worktop, 20×20G, Worktop length: 1500 mm



Order data

Order number	921014 1500
GTIN	4062406117894
Item class	9GG

Description

Version:

Workbench in sturdy steel construction with frame of rectangular hollow section. Drawer cabinet can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity. Feet with plastic pads, do not damage the floor.

Drawer bodies always RAL 7035 light grey, **powder coated**. Variable colours for the drawer fronts. No surrounding ledges, thereby allowing optimum cleaning and full availability of the area for drawer dividers (boxes, rigid foam inlays, slotted partitions). Drawer runner mountings at 25 mm intervals.

Locking system with 5-pin cylinder locks and modular barrels. Compatible with integrated locking systems.

Recessed open housing for ergonomic posture.

Fitted with:

Drawer front height (right) mm: 100, 125, 150, 250

Optional extras:

Additional accessories such as manual height adjustment, wheels, side panels, etc. can be found under GridLine individual components in Group 92.

Colour:

Cabinet body and drawer body RAL 7035 light grey, drawer fronts and cupboard doors RAL 7016 anthracite, **powder-coated**. **Drawer body not configurable, always RAL 7035 light grey.**

Workbench/desk load capacity - maximum distributed load (on wood): 800 kg

Drawer usable area in G: 20×20

Height: 950 mm

Worktop length: 1500 mm

Worktop depth: 750 mm
 Worktop thickness: 50 mm
 Support cabinet width: 1300 mm
 Support cabinet depth: 700 mm

Technical description

Support cabinet depth	700 mm
Drawer usable depth in G	20
Height	950 mm
Drawer usable area in G	20×20
Drawer body usable height	625 mm
Weight	139.8 kg
Worktop depth	750 mm
Worktop length	1500 mm
Support cabinet width	1300 mm
Number of drawers	4
Workbench/desk load capacity - maximum distributed load (on wood)	800 kg
Drawer usable depth	500 mm
Drawer usable width	500 mm
Drawer usable width in G	20
Worktop thickness	50 mm
Series	Ready-to-go
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel

Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	20x20G
Type of product	Complete workbench

Accessories

Overlay of plasticised PVC transparent Width 1500 mm	951951 1500
File set Number of tools 6	952253 6
Combination spanner set Number of tools 20	952505 20
Screwdriver set Number of tools 10	953521 10
Socket set 1/2 inch Number of tools 32	953821 32
Socket set 1/4 inch and 1/2 inch Number of tools 37	953828 37
Socket set 1/4 inch and 1/2 inch Number of tools 39	953833 39
Pliers set Number of tools 5	954295 5
Pliers set Number of tools 5	954305 5
Hammer set Number of tools 3	954690 3
Marking out and sawing Number of tools 8	954895 8
Drawer Drawer front height 100 mm	927800 100
Drawer Drawer front height 125 mm	927800 125
Drawer Drawer front height 150 mm	927800 150
Drawer Drawer front height 250 mm	927800 250
Lock plate for GridLine Type KO21	914227 KO21
Mat for drawers Dimension in G 20X20	951830 20X20
Non-slip mats set for drawers, 5 pieces Dimension in G 20X20	951885 20X20
Ribbed rubber mat for drawers Dimension in G 20X20	951910 20X20
Slotted dividers / plain dividers set Drawer front height / type 100/1	950320 100/1
	950320 100/2

Slotted dividers / plain dividers set Drawer front height / type 100/2	
Slotted dividers / plain dividers set Drawer front height / type 100/3	950320 100/3
Slotted dividers / plain dividers set Drawer front height / type 125/1	950320 125/1
Slotted dividers / plain dividers set Drawer front height / type 125/2	950320 125/2
Slotted dividers / plain dividers set Drawer front height / type 125/3	950320 125/3
Slotted dividers / plain dividers set Drawer front height / type 125/4	950320 125/4
Slotted dividers / plain dividers set Drawer front height / type 125/6	950320 125/6
Slotted dividers / plain dividers set Drawer front height / type 150/4	950320 150/4
Slotted dividers / plain dividers set Drawer front height / type 150/5	950320 150/5
Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
Workshop set Number of tools 22	955071 22
Workshop set Number of tools 26	955081 26
Lock barrel with 2 keys Lock number Ho (3-digit) 003	950050 003
Disassembly tool Type 1	950070 1