

Garant GRIDLINE

Vario workbench with 2 drawer casings 16G, height 950 mm, Eluplan worktop, dark, 12×20G, Worktop length: 1500/6+5mm**Order data**

Order number	922177 1500/6+5
GTIN	4062406118211
Item class	9GG

Description**Version:**

Workbench in sturdy steel construction. Drawer casing 16G can be locked centrally with cylinder lock. **100% full extension drawers** with differential runners and 75 kg load capacity.

Fitted with:

Drawer front height (left) mm: 75, 100, 100, 125, 150, 250

Drawer front height (right) mm: 75, 75, 150, 200, 300

Supplied with:

2 × drawer casings, worktop.

Colour:

Casing body, support legs and drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Drawer usable depth in G	20
Weight	177 kg
Drawer body depth	650 mm
Drawer usable depth	500 mm

Drawer body height	900 mm
Drawer usable width	300 mm
Drawer usable width in G	12
Drawer body width	400 mm
Worktop depth	750 mm
Worktop length	1500 mm
Workbench/desk load capacity - maximum distributed load (on wood)	1000 kg
Worktop thickness	50 mm
Series	vario
Drawer usable area in G	12×20
Height	950 mm
Number of drawers	11
Drawer body usable height	800 mm
Design version	Steel hollow section construction
Material thickness	1 mm
Workbench height	950 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension (partial/full extension)	100 %
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	12×20G
Type of product	Workbench

Accessories

Drawer Drawer front height 125 mm	927500 125
-----------------------------------	------------

Drawer Drawer front height 300 mm	927500 300
Drawer Drawer front height 100 mm	927500 100
Lock plate for GridLine Type KO21	914227 KO21
Drawer Drawer front height 75 mm	927500 75
Drawer Drawer front height 250 mm	927500 250
Drawer Drawer front height 150 mm	927500 150
Drawer Drawer front height 200 mm	927500 200
Drawer casing 16G with drawers Height / number of drawers 900/5	927300 900/5
Worktop with dark grey plastic coating (Eluplan) Worktop length 1500 mm	926241 1500
Drawer casing 16G with drawers Height / number of drawers 900/6	927300 900/6